

Garant
SNHX 12045 right-hand, Type: UNI

Order data

Order number	218605 UNI
GTIN	4062406538002
Item class	21A

Description
Note:

Standard application values for a_e max.

To machine a flat slot base, left and right inserts must be mounted on the carrier. The side facing away from the shank is equipped with left inserts.

Technical description

Type	UNI
Chamfer width	0.25 mm
Grade	HB7835
ISO code indexable insert	SNHX 12045
Tool material	Carbide
Insert thickness	4.5 mm
for slot width a_p	8 mm
Number of changes/inserts	4

Type of product

Indexable insert for milling