



## POLIFFAN-STRONG (ZA) abrasive flap disc for steel, 125 mm Ø, Grit: 50



### Order data

Order number	566322 50
GTIN	4007220777893
Item class	55P

### Description

#### Version:

Abrasive flap disc for demanding machining.

The patented design with **high coating density** for **high removal rate** and **tool life**.

### Technical description

Bore Ø	22.23 mm
Shape description	dished
Disc Ø	125 mm
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	125 mm Ø
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	Suitable		
Steel < 1400 N/mm <sup>2</sup>	Suitable		
Steel < 55 HRC	Suitable		
Steel < 60 HRC	Suitable		
Steel < 67 HRC	Suitable		
INOX	Suitable only under restricted conditions		
Ti	Suitable only under restricted conditions		
GG(G)	Suitable only under restricted conditions		
dry	Suitable		