

**Garant**
**ER collet chuck, ultra-short, SK 40, for ER collet size: 16**

**Order data**

Order number	300445 16
GTIN	4062406545352
Item class	31A

**Description**
**Version:**

Taper ground internally and externally. **Ultra-short type with internal precision clamping nut.** Best suited to working in restricted working areas, with higher stability.

**Application:**

For clamping tools with parallel shank in collets to DIN 6499 Form A and B.

**Supplied with:**

ER clamping nut (internal).

**Optional extras:**

ER collets No. 308941 – 309448, Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Note:**

Matching clamping nut No. 309621.

Machining strategy: HPC

Overhang dimension A: 27 mm

External Ø D: 24 mm

**Technical description**

External Ø D	24 mm
for ER collets	16 mm
Overhang dimension A	27 mm

Width across flats AF	19 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Collet chuck