

Garant
HiRunER precision ER collet chuck, SK 40 A = 160, for ER collet size: 11M

Order data

Order number	300645 11M
GTIN	4062406544577
Item class	31A

Description
Version:

External and internal tapers are ground. All shanks are hard turned for a smooth cutting action. Including Balluffchip bore, high-performance clamping nut up to 25000 rpm.

Advantage:

- **3 µm radial run-out with a 2 µm clamping nut, 6 µm radial run-out with a 5 µm clamping nut.**
- **Extremely strong holding force (up to factor 2 better than the standard ER chuck).**
- **Vibration reduction effect due to 2-part clamping nut (size 11M and 16M 1-piece).**

Application:

For clamping tools with plain shank in collets to DIN 6499 - Form A and B.

Supplied with:
Precision clamping nut.
Optional extras:

Pull studs (PS) No. 308600 – 308806,
 PS wrenches No. 308820 – 308835,
 ER collets No. 308901 – 309434,
 ER clamping wrenches No. 309748; 309749; 309758; 309759,
 Fahrion ER collets No. 308901 – 309434.

Note:

- **Clamps only nominal Ø up to shank Ø tolerance h 10.**
- **Do not use the clamping nut in combination with a sealing washer.**
- **Use in combination with Fahrion collets.**

Machining strategy: HSC

Clamping range: 1 - 7 mm

External Ø D: 16 mm

Spare ER clamping nut No. 309618: 11M

Technical description

Clamping range	1 - 7 mm
External Ø D	16 mm
Spare ER clamping nut No. 309618	11M
Adapter	SK 40 A = 160
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

HiRunER roller bearing wrench Type 11M	309757 11M
HiRunER roller bearing wrench for torque wrench Type 11M	309758 11M