

**Garant****Profile broaching holder  $\varnothing d = 32$  mm, Shank  $\varnothing DS: 25$ mm****Order data**

Order number	293102 25
GTIN	4062406560928
Item class	29K

**Description****Suitable for:**

CNC and conventional machines.

**Technical description**

Shank length $L_s$	50 mm
Shank type	Plain shank
L	41.5 mm
Shank $\varnothing D_s$	25 mm
$\varnothing D$	44 mm
$\varnothing d$	32 mm
Head length $L_1$	50 mm
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

