



## LED floodlight with CAS dimmer function, Type: NOVA-10



### Order data

Order number	081242 NOVA-10
GTIN	
Item class	07A

### Description

#### Version:

Cordless Alliance System (CAS) is a cross-manufacturer battery pack system of leading power tool brands.

High-performance cordless LED floodlight with dimmer function. The housing is made of injection-moulded aluminium and is extremely robust and resistant to strong blows, impacts and vibrations. For use with CAS 12V or 18V batteries or direct connection to SCANGRIP® power supplies (accessory).

- **BLUETOOTH light control enables up to four lights to be switched on/off and the light output to be adjusted in five levels to suit the respective task.**
- **With removable diffuser.**
- **Integral carrying handle and new base for flexible alignment and for direct mounting on the SCANGRIP® stand or with magnetic holders.**

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

**Lamps are supplied without battery and charger.**

#### Note:

Suitable batteries, chargers and power supply units for wired power supplies can be found under No. 081246 – 081249.

IP Index of Protection: IP 65

Illumination: 1000 - 10000 lm

Number of rechargeable batteries contained: 0

Type of rechargeable battery: Lithium-ion

Battery voltage: 18 V  
Battery voltage: 12 V  
Overall length: 305 mm

---

## Technical description

IP Index of Protection	IP 65
Power supply	Rechargeable battery-powered
Illumination	1000 - 10000 lm
Overall height	290 mm
Overall length	305 mm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Battery voltage	12 V
Overall width	125 mm
Number of rechargeable batteries contained	0
Manufacturer's designation	NOVA 10 CAS
Type of product	Floodlight