



Soldering fumes extraction Easy Arm 2, Number of filters/arms: 2



Order data

Order number	082304 2
GTIN	4003008095333
Item class	04K

Description

Version:

Visual and audible display for filter change. Identical filter for EASY ARM 1 and EASY ARM 2.

Interface for connecting i-CON soldering stations.

High extraction power – efficient filter performance – quiet operation. Filter the process air in 3 steps:

- **Pre-filter for dust and larger particles.**
- **Combination filter for micro-particles.**
- **Activated carbon filter absorbs harmful gases.**

The system is fitted using a suitable bench holder. Accessories such as extraction arms and nozzles can be found in the online shop under No. 082306 – 082313.

Extraction power is set on the system at the touch of a button, individually for each extraction arm.

electrostatic characteristic: EGB/ESD

Technical description

Extraction volume per arm	110 m ² /h
Overall width	255 mm
AC supply voltage	100 - 240 V
Overall height	470 mm

Overall length	490 mm
Weight	15 kg
Mains frequency	50 - 60 Hz
Power consumption	80 W
electrostatic characteristic	EGB/ESD
Type of product	Device for dust extract

Accessories

Combination filter, complete Type 1	082306 1
Extraction arm with joint Omniflex Type 1	082311 1
Extraction arm with joint for table mounting Highflex Type 1	082308 1
Extraction arm Highflex Type 1	082309 1
Pre-filter Type 1	082307 1
Plus extraction nozzle Type 1	082313 1
Extraction arm with joint Omniflex Type 1	082310 1
Rectangular extraction nozzle Type 1	082312 1
Combined Filter	OCA10-1001
Prefilter G4 pu 4 pcs.	OCA10-1002/04