

**Garant**
**Solid carbide chamfer mill 60°, uncoated, Ø e8 DC: 10mm**

**Order data**

Order number	208068 10
GTIN	4062406538194
Item class	11X

**Description**
**Version:**
**Tolerance:** Point angle  $\pm 1^\circ$ .

**Application:**

- Countersinking
- Chamfering

**Technical description**

Chamfer mill	30 degrees
Shank	DIN 6535 HB to h6
No. of teeth Z	2
Cutting edge $\varnothing D_c$	10 mm
Overall length L	72 mm
Flute length $L_c$	22 mm
Corner chamfer angle	30 degrees
Shank $\varnothing D_s$	10 mm
Feed $f_z$ for side milling in steel $< 900 \text{ N/mm}^2$	0.05 mm
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Type	N

Tolerance nominal $\varnothing$	e8
Helix angle	30 degrees
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Countersink tip angle	60 degrees
Through-coolant	no
Shank tolerance	h6
Colour ring	without
Type of product	Indexable end mill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	180 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	105 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	55 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	40 m/min	M
GG(G)	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

### Services

Shank grinding Type HB	129100 HB
------------------------	-----------

