

Garant**HiRunER precision ER collet chuck, HSK-A 63 short, for ER collet size: 20****Order data**

Order number	305523 20
GTIN	4062406545017
Item class	31A

Description**Version:**

External and internal tapers are ground. All shanks are hard turned for smooth running. Including RFID/Balluffchip bore, high-performance clamping nut up to 25000 rpm.

Advantage:

- **Excellent concentricity in the system (chuck + collet + clamping nut), 3 µm radial run-out with a 2 µm collet, 6 µm radial run-out with a 5 µm collet.**
- **Extremely strong holding force (up to factor 2 better than the standard ER chuck).**
- **Vibration reduction effect due to 2-part clamping nut (one part for mini version).**

Application:

For clamping tools with plain shank in collets to DIN 6499 - Form A and B.

Supplied with:

Precision clamping nut.

Optional extras:

Coolant tube No. 309880,

Socket wrench No. 309890,

ER collets Fahrion No. 308901 and 309432.

Hook wrench No. 628400, or torque wrench No. 309749 or No. 628520.

Note:

- **Clamps only nominal Ø up to shank Ø tolerance h 10.**
- **Do not use the clamping nut in combination with a sealing washer.**
- **Use the precision collet chuck always in conjunction with the precision clamping nut No. 309617; 309618.**
- **Use in combination with Fahrion collets.**
- **The blue design ring must be removed for Fahrion HP 2µm ER collets.**

Technical description

for ER collets	20
Overhang dimension A	75 mm
Clamping range	1 - 16 mm
External Ø D	38 mm
Spare ER clamping nut No. 309617	20
Clamping Ø D ₁	1-13 mm
Adapter	HSK-A 63 short
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Through-coolant	yes
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

HiRunER clamping wrench Type 20	309748 20
HiRunER clamping wrench for torque wrench Type 20	309749 20