

**Garant****ER collet chuck, ultra-short, SK 50, for ER collet size: 40****Order data**

Order number	300446 40
GTIN	4062406545376
Item class	31A

**Description****Version:**

Taper ground internally and externally. **Ultra-short type with internal precision clamping nut.** Best suited to working in restricted working areas, with higher stability.

**Application:**

For clamping tools with parallel shank in collets to DIN 6499 Form A and B.

**Supplied with:**

ER clamping nut (internal).

**Optional extras:**

ER collets No. 308941 – 309448, Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Note:**

Matching clamping nut No. 309621.

Machining strategy: HPC

Overhang dimension A: 29 mm

External  $\varnothing$  D: 50 mm

**Technical description**

External $\varnothing$ D	50 mm
for ER collets	40 mm
Overhang dimension A	29 mm

Suitable C-hook (pin) spanner No. 628400	45/50
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Collet chuck