



## Mini milling cutter HSS-Co8, uncoated, Ø e8 DC: 2mm



### Order data

Order number	191360 2
GTIN	4045197101976
Item class	12W

### Description

#### Version:

Centre cutting teeth for plunging.

**Eccentric relief ground.** Shank similar to DIN 1835 B with shank tolerance h6. General-purpose cutting edge geometry. For use as **slot drill or end mill** in side lock arbors and collet chucks.

**High cutting performance,** very competitive price. For milling keyways.

#### Note:

Save the regrinding costs: it is cheaper to use a mini slot drill to the limit of wear and throw it away, than to regrind it.

### Technical description

Cutting edge Ø $D_c$	2 mm
No. of teeth $Z$	3
Feed $f_z$ for slot milling in steel < 750 N/mm <sup>2</sup>	0.003 mm
Shank Ø $D_s$	6 mm
Overall length $L$	35 mm
Flute length $L_c$	4 mm
Direction of infeed	horizontal, oblique and vertical
Shank	HB with h6
Tolerance nominal Ø	e8
Helix angle	30 degrees

Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	HSS Co 8
Standard	Manufacturer's standard
Type	N
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	83 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
CuZn	suitable only under restricted conditions	55 m/min	N
wet maximum	suitable		