

Garant**Adapter $\varnothing d = 32$ mm, Shank $\varnothing D_s$: 16mm****Order data**

Order number	293105 16
GTIN	4062406560959
Item class	29K

Description**Application:**

With this adapter, cutter inserts for outer profiles can also be used in conjunction with a profile broaching holder for inner profiles.

Suitable for:

Profile broaching holder for internal profiles No. 293026, 293033, 293076.

Note:

For reasons of stability, use the profile broaching holder No. 293102 on higher batch sizes or materials that are difficult to machine.

Technical description

Shank $\varnothing D_s$	16 mm
$\varnothing d$	32 mm
Profile length t_{max}	20 (from 10 AF) mm
Profile length t_{max}	31 (up to 8 AF) mm
Shank length L_s	19 mm

Head length L ₁	40.5 mm
L	32 mm
Type of product	Keyway broaching and profile slotting tool