



Cordless polishing machine, Type: M18FAP180



Order data

Order number	077773 M18FAP180
GTIN	4002395144525
Item class	03L

Description

Version:

M18 FUEL™ **cordless polisher** with 8-stage speed pre-selection (range from 360 – 2200 rpm).
Electronic speed control with soft start for optimum control.

Supplied with:

Supplied with 2 pcs. batteries 18 V / 5 Ah, charger, AVS additional handle, grasp handle and polishing pad.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Battery capacity	5 Ah
Power supply	Rechargeable battery-powered
Weight	2 kg
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Battery voltage	18 V
Manufacturer's designation	M18 FAP180-502X
Toolholder	M14

Speed range	360 - 2200 min ⁻¹
Power consumption	1400 W
maximum polishing tool Ø	180
Type of product	Polishing machine

Accessories

Li-ion system M18B5 Battery type MB18	073816 MB18
Battery starter set Type M18NRG5	073839 M18NRG5