


HOLEX Pro INOX M solid carbide milling cutter HPC, TiSiN, Ø e8 DC: 20mm

Order data

Order number	202996 20
GTIN	4062406569204
Item class	12Y

Description
Version:

Outstanding tool life in its class for machining **corrosion-resistant steels** thanks to **innovative coating and geometry**. Especially for **stainless steels in the high-performance range**, e.g. duplex. **Optimal metal removal rate** due to **high cutting speeds**.

Technical description

Feed f_z for side milling in INOX $> 900 \text{ N/mm}^2$	0.09 mm
Cutting edge $\varnothing D_c$	20 mm
Shank	DIN 6535 HB to h6
Overhang length L_1 incl. recess	74 mm
Direction of infeed	horizontal, oblique and vertical
Overall length L	126 mm
No. of teeth Z	4
Recess $\varnothing D_1$	19.5 mm
Tolerance nominal \varnothing	e8
Helix angle	38 degrees
Flute length L_c	60 mm
Feed f_z for slot milling in stainless steel $> 900 \text{ N/mm}^2$	0.07 mm
Corner chamfer angle	45 degrees

Shank $\varnothing D_s$	20 mm
Corner chamfer width at 45°	0.3 mm
Series	Pro Inox
Coating	TiSiN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0,08×D
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P
TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm ²	suitable	100 m/min	M
INOX > 900 N/mm ²	suitable	85 m/min	M

Uni	suitable only under restricted conditions
wet maximum	suitable
wet minimum	suitable
dry	suitable only under restricted conditions
Air	suitable only under restricted conditions