


Garant

GARANT Master Ni-Based solid carbide milling cutter HPC / TPC, TiAlN, Ø DC: 6mm



Order data

Order number	203048 6
GTIN	4062406565718
Item class	11Z

Description

Version:

Specially ground with **corner radii similar to torus cutters**.
Innovative substrate specially for machining **nickel-based alloys**. Newly developed coating.

Application:

For milling **nickel-based alloys with high red hardness**.

Note:

Successor product to No. 203028.

Technical description

Tolerance nominal Ø	e8
Corner rounding r_v	0.2 mm
Helix angle	35 degrees
Direction of infeed	horizontal, oblique and vertical
Recess Ø D_1	5.8 mm
Overhang length L_1 incl. recess	19 mm
Feed f_z for side milling in Inconel®	0.05 mm
No. of teeth Z	4
Cutting edge Ø D_c	6 mm
Flute length L_c	13 mm

Shank $\varnothing D_s$	6 mm
Overall length L	57 mm
Shank	DIN 6535 HB to h6
Series	Master Ni-based
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0,08×D
Through-coolant	no
Machining strategy	TPC
Machining strategy	HPC
Colour ring	pink
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Inconel	suitable	40 m/min	S
wet maximum	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------