


Garant

GARANT Master Ni-Based solid carbide milling cutter HPC/TPC, TiAlN, Ø e8 DC: 10mm



Order data

Order number	203161 10
GTIN	4062406565817
Item class	11Z

Description

Version:

Specially ground with **Torus-like corner radius**.

Innovative substrate specially for machining **nickel-based alloys**. Newly developed coating.

Application:

For milling **nickel-based alloys with high red hardness**.

Note:

Successor product to No. 203082.

Technical description

Shank	DIN 6535 HB to h6
Corner rounding r_v	0.2 mm
Balance quality with shank	G 2.5 with HB
No. of teeth Z	5
Overhang length L_1 incl. recess	30 mm
Helix angle	38 degrees
Flute length L_c	22 mm
Feed f_z for side milling in Inconel®	0.07 mm
Direction of infeed	horizontal, oblique and vertical
Shank $\varnothing D_s$	10 mm

Overall length L	72 mm
Tolerance nominal \varnothing	e8
Cutting edge $\varnothing D_c$	10 mm
Recess $\varnothing D_1$	9.7 mm
Series	Master Ni-based
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	0,08×D
Through-coolant	no
Machining strategy	HPC
Machining strategy	HPC
Colour ring	pink
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Inconel	suitable	40 m/min	S
wet maximum	suitable		