



Cordless compact bandsaw, Type: M12FBS64



Order data

Order number	078202 M12FBS64
GTIN	4058546346324
Item class	03L

Description

Version:

FUEL™ compact powerful cordless bandsaw with brushless POWERSTATE™ motor for mobile sawing for improved handling characteristics.

- **Easy band saw blade change without using tools.**
- **Steplessly variable saw blade speed control with speed switch.**
- **Sturdy metal frame, metal hook.**
- **LED illumination of the cutting area.**

Supplied with:

Supplied with 2 pcs. M12 B4 batteries, charger, transport case.

Note:

For matching spare batteries and accessories see No. 073816 and 073809. Suitable saw blades available on request.

Technical description

Band saw length	776 mm
Weight	3.2 kg

Battery voltage	12 V
Belt speed	0 - 116 m/min
Battery capacity	4 Ah
Power supply	Rechargeable battery-powered
maximum cutting depth 90°	64 mm
Number of rechargeable batteries contained	2
maximum vibration to EN	< 2.5 m/s ²
Manufacturer's designation	M12FBS64
Type of rechargeable battery	Lithium-ion
Band saw width	13 mm
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 12 V
Type of product	Saw

Accessories

Battery starter set Type M12NRG4	073839 M12NRG4
Li-ion system M12B4 Battery type MB12	073815 MB12
Battery charger Type M1218SC	073840 M1218SC
Li-ion system M12B6 Battery type MB12	073829 MB12
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12