

Garant

GARANT Power Q Mini high feed rate indexable milling cutter, with bore, Ø D / number of effective cutting edges Z: 40/7mm


Order data

Order number	213058 40/7
GTIN	4062406566722
Item class	210

Description
Version:

High feed rate milling system for **smaller machining diameters** and **greater operating depths**. Particularly **effective due to the large number of cutting edges**.

Spare part:

Pack of insert screws No. 219799 9 (7IP; 1.2Nm).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 7IP**.

Technical description

Ramping angle α_{\max}	0.62 degrees
Setting angle κ	20 degrees
Ø D ₃	34 mm
Through-coolant	yes
suitable indexable insert	ANGX10T308ZE.R
Circular interpolation milling a _p	1 mm

Mounting bore \varnothing	16 mm
Number of cutting edges Z	7
Ramping length L for α_{\max}	32.4 mm
Circular interpolation milling $\varnothing D_{\min}$	74 mm
Overall length L_{tot}	40 mm
Circular interpolation milling $\varnothing D_{\max}$	78 mm
Cutting edge $\varnothing D_c$	40 mm
Series	Power Q
Fz Helix	0.8
Shank type	with bore
Milling application	Circular milling
Milling application	Plunging
Milling application	Circular milling
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill