



Cordless hammer drill / driver, Type: GSB1235



Order data

Order number	070104 GSB1235
GTIN	4059952513966
Item class	03B

Description

Version:

Bosch cordless hammer drill / driver for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

Sturdy and handy cordless drill / driver, only **1 kg** in weight.

Supplied with:

Supplied with 2× Li-ion batteries, charger and transport bag.

Note:

See from No. 073851 and 073866 for suitable replacement batteries and chargers.

Technical description

Battery voltage	12 V
maximum speed 1st speed	0 - 460 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 12 V
maximum twist drill size Ø in wood	32 mm

Quick-clamping chuck range	1 - 10 mm
maximum twist drill size Ø in concrete	10 mm
maximum speed 2nd speed	1750 min ⁻¹
Type of rechargeable battery	Lithium-ion
typical application	Medium
maximum twist drill size Ø in steel	10 mm
maximum vibration to EN without hammer drill function	<2.5 m/s ²
Battery capacity	3 Ah
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	2
Manufacturer's designation	GSB 12V-35
maximum torque soft	20 Nm
Motor design	Brushless motor
maximum torque hard	35 Nm
Weight	1 kg
maximum vibration to EN with hammer drill function	10.5 m/s ²
Type of product	limpact drill /screwdriver

Accessories

Li-ion battery Battery type, battery voltage B12 V	073855 B12
Battery charger Type GAL1240	073866 GAL1240