



## Cordless impact wrench / impact driver, Type: M18ONEFFDS



### Order data

Order number	074010 M18ONEFFDS
GTIN	4058546324681
Item class	03L

### Description

#### Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. M18 FUEL™ ONEKEY™ 1 inch cordless impact wrench / impact driver with snap ring provides up to 2576 Nm of tightening torque and replaces wired, petrol and pneumatic devices. DRIVE CONTROL enables quick switching between the 4 available settings with different speeds and torques.

- **ONE KEY™ app for individualising the tool settings.**
- **ONE KEY™ tool tracker & security permits amongst other things a display of the latest position of the device.**

#### Version of the advertising text:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

**Supplied with:**

1 pc. M18 HB12 12.0 Ah battery pack, M12-18 FC charger, carrying case.

**Note:**

For matching spare batteries and accessories see from No. 073808.

---

**Technical description**

Number of impacts 4th setting	0 - 1440 min <sup>-1</sup>
maximum torque 3rd step	1966 Nm
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Weight	11.1 kg
maximum torque 4th setting	2576 Nm
Packaging	Modular case (HD=Heavy Duty)
Battery capacity	12 Ah
Number of impacts 3rd stage	0 - 1200 min <sup>-1</sup>
Number of impacts 2nd stage	0 - 930 min <sup>-1</sup>
Battery voltage	18 V
Tool arbor drive profile	External square drive
Manufacturer's designation	M18 ONEFH1WF1DS-121C
App link	OneKey
Number of impacts 1st stage	0 - 750 min <sup>-1</sup>
Tool arbor size	1 in
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum screw Ø (8.8 - 12.9)	M42
Type of rechargeable battery	Lithium-ion
maximum torque 2nd step	1254 Nm
typical application	Heavy Duty
maximum torque 1st step	1180 Nm
Type of product	Impact wrench

---

## Accessories

Battery charger Type FE80-BC

073845 FE80-BC