


**HOLEX Pro UNI solid carbide milling cutter HPC, TiSiN, Ø e8 DC: 16mm**

**Order data**

Order number	203068 16
GTIN	4062406572266
Item class	12Y

**Description**
**Version:**

For **roughing and finishing at very high feed rates** with smooth cutting action. **Newly developed geometry and high-performance coating** for excellent production results with maximum tool life in various materials. **High intrinsic stability** and smooth cutting action due to unequal spacing.

**Technical description**

Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.08 mm
Helix angle	42 degrees
Feed $f_z$ for side milling in INOX > 900 N/mm <sup>2</sup>	0.06 mm
Shank	DIN 6535 HB to h6
Corner chamfer width at 45°	0.3 mm
Corner chamfer angle	45 degrees
Feed $f_z$ for slot milling in stainless steel > 900 N/mm <sup>2</sup>	0.05 mm
Overall length L	92 mm
Cutting edge Ø $D_c$	16 mm
Tolerance nominal Ø	e8
Shank Ø $D_s$	16 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.1 mm

No. of teeth Z	4
Flute length $L_c$	36 mm
Recess $\varnothing D_1$	15.5 mm
Direction of infeed	horizontal, oblique and vertical
Overhang length $L_1$ incl. recess	42 mm
Series	Pro Uni
Coating	TiSiN
Tool material	solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Machining strategy	MTC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	250 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	140 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable	80 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable	240 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		