

**3M****Velour-backed abrasive disc 237AA (A), Ø 115 mm, Grit: 180****Order data**

Order number	567724 180
GTIN	2050002053311
Item class	51E

**Description****Version:**

The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

237AA Trizact™ with fine-structured pyramidal surface of micro-Aluminium Oxide mineral particles (A).

**Application:**

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

For a **fine and uniform surface finish** all steels, stainless steels, brass and titanium alloys. Specially for contour grinding and preparation for polishing.

**Note:**

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

**Technical description**

3M grit designation	A100
---------------------	------

Disc Ø	115 mm
Grit	180
Manufacturer's designation	237AA Trizact™
Series	237AA
Grinding media	Aluminium oxide mineral particles (A)
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Propulsive equipment	Angle grinder
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
dry	suitable		