

Garant

Abrasive flap disc long life ZA, flat, Ø 115 mm, Grit: 40



Order data

Order number	565269 40
GTIN	4062406570408
Item class	51M

Description

Version:

- Premium zirconium aluminium oxide (ZA) for maximum abrasive performance.
- Sturdy polyester cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.
- Sturdy glass fibre pad for optimum contact pressure.
- Suitable for both steel and stainless steel.
- Best results on low-power and high-power angle grinders.

long life - very closely spaced flap strips, for **maximum tool life**.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Technical description

Grit	40
Disc Ø	115 mm
Shape description	flat

Bore Ø	22.23 mm
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		
dry	suitable		