


Garant**Centring vice, automation, Jaw width A: 80Amm****Order data**

Order number	360134 80A
GTIN	4062406572600
Item class	30N

Description**Version:**

Centring vice for flexible applications.

- **Absolute operational reliability thanks to enclosure.**
- **High repetition accuracy 0.02 mm.**
- **Variable central alignment ± 0.02 mm.**
- **Functional faces hardened.**
- **Sturdy design of tool steel, surface protection by brief exposure nitriding.**

Advantage:

- **Flexible lightweight.**

Multi-functional uses.

Application:

Ideal for 5-face machining, perfect for clamping blank parts.

Suitable for:

Automation extension base No. 360164.

Supplied with:

Supplied with socket No. 642700 size E12.

Supplied with 4 clamping studs size 90.

Optional extras:

Types of jaws No. 360135– 360151.

Technical description

Length	120 mm
Jaw width A	80 mm
Torque	40 Nm
Width	120 mm
Stroke	22 mm
Clamping force up to maximum	17 kN
Weight	3.5 kg
Height	50 mm
suitable for colour code	ZC 80
Type of product	Machine vice