


Garant
Solid carbide roughing end mill MTC, TiAlN, Ø d11 DC: 14mm

Order data

Order number	205710 14
GTIN	4045197362629
Item class	11X

Description
Version:

Dimensions similar to DIN 6527.

Optimised special knuckle profile for roughing.

Very **high rate of metal removal.**

Can be used as a **universal end mill.**

Application:

Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres.

Technical description

Cutting edge Ø D _c	14 mm
Corner chamfer width at 45°	0.3 mm
Feed f _z for slot milling in steel < 900 N/mm ²	0.08 mm
Feed f _z for side milling in steel < 900 N/mm ²	0.09 mm
No. of teeth Z	4
Shank Ø D _s	14 mm
Overall length L	75 mm
Flute length L _c	16 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	d11

Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	MTC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 750 N/mm ²	suitable	170 m/min	P
Steel < 900 N/mm ²	suitable	170 m/min	P
Steel < 1100 N/mm ²	suitable	140 m/min	P
Steel < 1400 N/mm ²	suitable	120 m/min	P
INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	50 m/min	M
Ti > 850 N/mm ²	suitable	40 m/min	S
GG(G)	suitable	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air

Suitable only under
restricted conditions