

## Garant

### Solid carbide roughing end mill MTC, TiAlN, Ø d11 DC: 8mm



#### Order data

Order number	205714 8
GTIN	4045197362735
Item class	11X

#### Description

##### Version:

Dimensions similar to DIN 6527.

##### Optimised special knuckle profile for roughing.

Very **high rate of metal removal**.

##### Application:

Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres.

#### Technical description

Recess Ø D <sub>1</sub>	7.5 mm
Corner chamfer width at 45°	0.2 mm
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.04 mm
No. of teeth Z	4
Cutting edge Ø D <sub>c</sub>	8 mm
Overhang length L <sub>1</sub> incl. recess	26 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.05 mm
Shank Ø D <sub>s</sub>	8 mm
Overall length L	63 mm
Flute length L <sub>c</sub>	16 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6

Tolerance nominal $\varnothing$	d11
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	MTC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	120 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	60 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	45 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air

suitable