

**KERN****Precision scales, type FCB, maximum weighing range: 30000g**

---

## Order data

Order number	479512 30000
GTIN	4045761202665
Item class	47D

---

## Description

### Version:

- **Selectable mains and battery operation. Auto-off after 3 minutes.**
- **CAL calibration programme: For accuracy adjustment (required external calibration weight available on request).**
- **Quantity counting: Reference quantities selectable 5, 10, 25, 50 pieces. Display selectable between pieces and weight.**
- **Formulation weighing: Separate memory for weight of the tare vessel and of the formulation ingredients (net totals).**

KERN Universal Port (KUP): allows the connection of external KUP interface adapters, such as RS-232 or USB, for exchanging data and control commands, without installation effort.

Second display on the rear of the scales.

### Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood.

### Optional extras:

Battery No. 081561 size 6LR61; internal rechargeable battery on request. Data cable, printer on request.

### Attention:

German version. Order free UK adapter plug No. 08 1174\_GB.

---

## Technical description

---

Depth	323 mm
Reproducibility	0.2 g
Width	270 mm
Dimensions of weighing plate	253×227 mm
Settling time	3 s
Scale divisions	0.2 g
Power supply	Battery-powered
Power supply	Rechargeable battery-powered
Minimum unit weight	2 g
maximum weighing range	0 - 30000 g
Height	110 mm
Manufacturer's designation	FCB
Net weight	2.6 kg
Linearity	±0.6 g
Calibration	K2
Type of product	Precision balance

---

## Services

DAkkS calibrationScales maximum weighing range 50	027710 50
CalibrationScales maximum weighing range 50 kg	027700 50