

KERN**Platform scales, type EOC, maximum weighing range: 300Lkg**

Order data

Order number	479606 300L
GTIN	4045761192294
Item class	47D

Description

Version:

- **Robust stainless steel platform scales can be used as parcel, industrial, and counting scales.**
- **Dual-range scales with automatic changeover between the ranges (more precise display in the lower half of the weighing range).**
- **Display unit with numeral height 24 mm can be remote from platform; can be stood or mounted using flexible cable.**
- **High mobility due to optional battery operation and compact design.**
- **Provides an optical and acoustic signal to support portioning, metering or sorting within the tolerance range.**
- **Percentage determination: Enable weighing out to a prescribed value (100%) and determination of deviations from that set value.**
- **Quantity counting: Easy counting function allows quick counting of large numbers. Reference quantities selectable 5, 10, 25, 50 pieces.**
- **CAL calibration programme: For setting the accuracy (external calibration weight required for this available on request).**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with mains adapter, table base including wall bracket, protective hood.

Technical description

Reading at top of weighing range	100 g
Minimum unit weight	100 g
maximum weighing range	0 - 300 kg
Scale divisions	50 g
Net weight	18.4 kg
Calibration	Price on request
Manufacturer's designation	Type EOC
Power supply	Battery-powered
Settling time	2 s
Reproducibility	100 g
Dimensions of weighing plate	600×500 mm
IP Index of Protection	IP 65
Interface	RS232C interface
Type of product	Platform balance