

Garant
Shoulder mill 90°, with threaded shank, Ø D / number of teeth Z: 32/5mm

Order data

Order number	215178 32/5
GTIN	4062406570118
Item class	210

Description
Version:

The corner milling system for **stepless shoulder milling**. The compact insert size ensures **immense stability** with an extra-high number of cutting edges – resulting in **very high productivity**.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 7IP**.

Technical description

Ø D ₁ h6	17 mm
Number of cutting edges Z	5
Pack of insert screws	219878 1 (7IP; 1.2 Nm)
suitable indexable insert	XNEX 040308
Cutting edge Ø D _c	32 mm
Overall length L _{tot}	40 mm
Ø D ₂	28.7 mm
Mounting thread M	M16
maximum cutting depth a _{p,max}	2 mm
Shank type	with threaded shank

Setting angle κ	90 degrees
Milling application	Ramping
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Set of insert screws 10 pieces Type 1	219878 1
---------------------------------------	----------