



Cordless core drilling machine, Type: M18FMDP



Order data

Order number	076528 M18FMDP
GTIN	4002395136650
Item class	03L

Description

Version:

M18 FUEL™ rechargeable battery magnetic core drilling machine with LED illumination.

- **Core drilling up to 38 mm.**
- **2-speed gearbox: optimised speed for drilling with core drills (400 rpm) and jobber drills (690 rpm).**
- **Strong permanent magnet with holding force of 8890 N.**
- **Version with REDLINK PLUS™ electronics AUTOSTOP™.**
- **Integral magnetic coolant container.**

Supplied with:

2 x M18 B5 battery packs, M12-18 FC charger, carrying case.

Note:

Suitable carbide core drills can be found from No. 118780. Suitable rechargeable battery with No. 073816 size MB18 and No. 073839 size M18NRG5 available.

Technical description

Type of rechargeable battery	Lithium-ion
Battery voltage	18 V

maximum twist drill size Ø in steel	13 mm
Packaging	Carrying case
Power supply	Battery-powered
Boring depth	Core drills in steel maximum 50 mm
Height	552 mm
Weight	13.9 kg
maximum reamer Ø	18 mm
maximum speed	400 - 690 min ⁻¹
Length of magnetic base	170 mm
Tool arbor shape	19 mm Weldon
Battery capacity	5 Ah
maximum countersink Ø	38 mm
Width of the magnetic base	65 mm
Working stroke	146 mm
Manufacturer's designation	M18 FMDP-0C
Number of rechargeable batteries contained	2
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Drill

Accessories

Battery starter set Type M18NRG5	073839 M18NRG5
Li-ion system M18B5 Battery type MB18	073816 MB18