



## Cordless ratchet, Type: M12FHIR38



### Order data

|              |                  |
|--------------|------------------|
| Order number | 070228 M12FHIR38 |
| GTIN         | 4058546341053    |
| Item class   | 03L              |

### Description

#### Version:

**MILWAUKEE – cordless right angle drill and ratchet**

- **REDLINK™ electronics with stepless speed control, reversible running and overload protection.**
- **LED illumination of the working area.**
- **Red Li-ion batteries with single-cell monitoring and charge display.**

#### Supplied with:

**Without battery and without charger.**

#### Note:

See No. 073814 and No. 073839 for suitable batteries and chargers.

### Technical description

|  |                       |
|--|-----------------------|
| maximum torque hard                                  | 47 Nm                 |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 12 V |
| Format   | Impact ratchet        |
| Manufacturer's designation                           | M12FHIR38             |

|  |                           |
|--|---------------------------|
| Type of rechargeable battery               | Lithium-ion               |
| Battery voltage                            | 12 V                      |
| Weight                                     | 1.4 kg                    |
| Toolholder                                 | Square 3/8 inch           |
| maximum speed 1st speed                    | 0 - 450 min <sup>-1</sup> |
| Battery capacity                           | 2 Ah                      |
| typical application                        | Strong                    |
| maximum vibration to EN                    | <2.5 m/s <sup>2</sup>     |
| Number of rechargeable batteries contained | 0                         |
| Type of product                            | Screwdriver               |

---

## Accessories

|  |             |
|--|-------------|
| Li-ion system M4B2/M12B2 Battery type MB12 | 073814 MB12 |
|--|-------------|