


Garant**Centring vice, automation, Jaw width A: 120Amm****Order data**

Order number	360134 120A
GTIN	4062406572914
Item class	30N

Description**Version:**

Centring vice for flexible applications.

- **Absolute operational reliability thanks to enclosure.**
- **High repetition accuracy 0.02 mm.**
- **Variable central alignment ± 0.02 mm.**
- **Functional faces hardened.**
- **Sturdy design of tool steel, surface protection by brief exposure nitriding.**

Advantage:

- **Flexible lightweight.**

Multi-functional uses.

Application:

Ideal for 5-face machining, perfect for clamping blank parts.

Suitable for:

Automation extension base No. 360164.

Supplied with:

Supplied with socket No. 642700 size E12.

Supplied with 4 clamping studs size 90.

Optional extras:

Types of jaws No. 360135– 360151.

Technical description

Torque	60 Nm
Length	130 mm
Width	120 mm
Jaw width A	120 mm
Stroke	25 mm
Clamping force up to maximum	25.5 kN
Height	50 mm
Weight	5.3 kg
suitable for colour code	ZC120
Type of product	Machine vice