

**Garant****Centring vice, pneumatic, Type: 100/4****Order data**

|              |               |
|--------------|---------------|
| Order number | 360180 100/4  |
| GTIN         | 4062406572952 |
| Item class   | 310           |

**Description****Version:**

- **Adjustable stroke + 5 mm per end.**
- **Clamping force steplessly adjustable up to 22.5 kN. Arithmetical sum = 45 kN.**
- **Even if the compressed air supply fails, the centring vice maintains a slight (approx. 60 kg) pre-load, to ensure secure positioning of the workpiece, such as when a shuttle table is being used.**

With base plate, for higher support torque and maximum stability.

**Application:**

For centralised clamping of components. Suitable for **automated operation** with 4-channel clamping pots, even with side connections.

**Optional extras:**

Range of jaws no. 360135 - 360151 size 80.

**Technical description**

|             |         |
|-------------|---------|
| Jaw width A | 80 mm   |
| Weight      | 14.8 kg |
| L           | 100 mm  |
| B           | 100 mm  |

|                               |              |
|-------------------------------|--------------|
| Maximum compressed air supply | 9 bar        |
| Clamping range                | 6 mm         |
| Clamping force up to maximum  | 10 kN        |
| Height H                      | 95 mm        |
| suitable for colour code      | PCV 100      |
| Dimension across diagonals    | 200 mm       |
| Type of product               | Machine vice |