

Garant
Revolvinglathe centre for insert, Type: 32

Order data

Order number	320617 32
GTIN	4062406573133
Item class	31Z

Description
Version:

- **Sprung version for axial length compensation whilst machining.**
- **Fully hardened and ground. Maintenance-free due to lifetime lubrication.**
- **Special seal prevents ingress of dirt and coolant.**

Plain shank for clamping in boring bar holders, collet chucks or hydraulic chucks; for mounting in the second turret.

For machining heavy components.

Description:

Lathe centres are mainly used on lathes to support long and slim workpieces, since with these workpieces there would otherwise be a risk of the workpiece bending or moving around as a result of the forces generated.

The lathe centre is secured with a Morse taper. The workpiece is clamped in the chuck and a counterbore is added using a centre drill. After re-clamping, the lathe centre is then inserted.

Application:

Flexible application thanks to exchangeable inserts. For general use on turrets and counter-spindles on CNC machines.

Optional extras:

Exchangeable inserts No. 320625. Exchangeable inserts No. 320629.

Note:

Changing the inserts in the key surfaces by counter-rotation.

Technical description

Sprung travel	4 mm
---------------	------

Reach L ₁	95 mm
for workpiece weight	500 kg
Overall length L	155 mm
Body Ø D	66 mm
Ø d	32 mm
Radial run-out	0.01 mm
Shank Ø D ₁	18 mm
suitable for colour code	K18
maximum speed	5000 min ⁻¹
Adapter	Shank Ø 32 mm
Type of product	Centring drill