



Mini milling cutter HSS-Co8, uncoated, Ø e8 DC: 7,5mm



Order data

| | |
|--------------|---------------|
| Order number | 191360 7,5 |
| GTIN | 4045197102140 |
| Item class | 12W |

Description

Version:

Centre cutting teeth for plunging.

Eccentric relief ground. Shank similar to DIN 1835 B with shank tolerance h6. General-purpose cutting edge geometry. For use as **slot drill or end mill** in side lock arbors and collet chucks.

High cutting performance, very competitive price. For milling keyways.

Note:

Save the regrinding costs: it is cheaper to use a mini slot drill to the limit of wear and throw it away, than to regrind it.

Technical description

| | |
|--|----------------------------------|
| No. of teeth Z | 3 |
| Feed f_z for slot milling in steel < 750 N/mm ² | 0.014 mm |
| Cutting edge Ø D _c | 7.5 mm |
| Shank Ø D _s | 8 mm |
| Overall length L | 42 mm |
| Flute length L _c | 10 mm |
| Direction of infeed | horizontal, oblique and vertical |
| Shank | HB with h6 |
| Tolerance nominal Ø | e8 |
| Helix angle | 30 degrees |

| | |
|----------------------|-------------------------|
| Corner chamfer angle | 90 degrees |
| Coating | uncoated |
| Tool material | HSS Co 8 |
| Standard | Manufacturer's standard |
| Type | N |
| Through-coolant | no |
| Colour ring | without |
| Type of product | End / face mill |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 83 m/min | N |
| Steel < 500 N/mm ² | suitable | 30 m/min | P |
| Steel < 750 N/mm ² | suitable | 25 m/min | P |
| Steel < 900 N/mm ² | suitable | 25 m/min | P |
| CuZn | suitable only under restricted conditions | 55 m/min | N |
| wet maximum | suitable | | |