



**Solid carbide roughing end mill HPC, TiXSi, Ø f8 DC: 8mm**

**Order data**

Order number	203044 8
GTIN	4045197679376
Item class	12X

**Description**
**Version:**

For **roughing and finishing**.

Up to 1.5×D into solid material **at very high feed rates** with smooth cutting action.

**Advantage:**

Optimised flute form, eccentric relief ground, wide chip space.

**Technical description**

Recess Ø D <sub>1</sub>	7.7 mm
Corner chamfer width at 45°	0.2 mm
Overhang length L <sub>1</sub> incl. recess	25 mm
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.05 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.06 mm
Cutting edge Ø D <sub>c</sub>	8 mm
No. of teeth Z	4
Shank Ø D <sub>s</sub>	8 mm
Overall length L	63 mm
Flute length L <sub>c</sub>	21 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8

Helix angle	38 degrees
Corner chamfer angle	45 degrees
Coating	TiXSi
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	250 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	200 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	160 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	70 m/min	M
GG(G)	suitable only under restricted conditions	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		

Air

suitable