



## Cordless stapler, Manufacturer's designation: M12BST



### Order data

Order number	078402 M12BST
GTIN	4058546028077
Item class	03L

### Description

#### Version:

Compact and powerful M12™ **cordless stapler** with integral staple insertion slide and non-slip grip. Up to 2000 staples per 2.0 Ah battery charge. Function to prevent accidental operation.

#### Suitable for:

Type G staples with maximum insertion depth of 6–14 mm.

#### Supplied with:

Supplied with 2 pcs. 12 V / 2.0 Ah batteries, C12 C charger, HD box.

### Technical description

Manufacturer's designation	M12BST
maximum staple insertion depth	14 mm
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
suitable type of staple	G

Battery capacity	2 Ah
Battery voltage	12 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Carrying case
Type of product	Tacker

---

## Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12