

Pneumatic-hydraulic pop rivet tool, Type: RAC182



Order data

Order number	770513 RAC182
GTIN	8033371219216
Item class	72E

Description

Version:

Operating pressure 6 – 7 bar. Removable rivet pin capture box. Powerful and reliable pop riveter. Quick and reliable securing of pop rivets due to the powerful gripping system (grips the rivet pin without slipping). Variably adjustable suction to dispose the snapped rivet pins into the capture box.

Supplied with:

Nozzles (suitable for steel, stainless steel, aluminium, copper): 2.4; 2.4-3.4 and 4.8 mm. Nozzle (suitable for aluminium): 6 mm. 1 bottle hydraulic oil 50 ml.

Technical description

Weight	1.7 kg
for pop rivets aluminium up to	6 mm
Hose connection	8 mm
Tool stroke	20.5 mm
Setting force at 6 bar	10500 N
maximum mandrel Ø	3.5 mm

Air consumption per rivet	5.1 l
for pop rivets in all materials up to	4.8 mm
Operating pressure	6 - 7 bar
Type of product	Pop riveter