

**Garant****DCGW 04T001, Cutting edge version: N****Order data**

Order number	268098 N
GTIN	4062406575984
Item class	21L

**Description****Version:**

PCD version.

**Technical description**

Cutting conditions	slightly interrupted
Main application	N
Cutting depth $a_p$	0.05 - 1 mm
Number of changes/inserts	1
Cutting speed $v_c$ main application	120 - 800 m/min
ISO code indexable insert	DCGW 04T001
Tool material	PCD
Grade	PCD
Corner radius	0.1 mm

Cutting edge version	N
Finishing/roughing assignment	Finishing
Feed f	0.03 - 0.035 mm/rev.
Type of product	Indexable insert for turning