



Cordless compressor, Type: M18FAC



Order data

Order number	079844 M18FAC
GTIN	4058546325626
Item class	03L

Description

Version:

M18 FUEL™ cordless compressor. Conventional nailers and tackers can be operated with an air pressure of 2.8 bar and an effective delivery quantity of 48 l/m. Sound pressure level of only 68 dB(A) for pleasant working conditions.

Supplied with:

Version without batteries and without charger.

Note:

Other workshop compressors available on request.

See No. 073833 size M18HNRG12 for suitable battery starter set.

Technical description

Weight	14.4 kg
Power consumption	0.4 kW
maximum pressure (air)	9.31 bar
maximum suction rate	126 l/min
Manufacturer's designation	M18FAC

Operating noise	68 dB(A)
Width	500 mm
maximum filling rate	74 l/min
Length	500 mm
Height	500 mm
Pressure vessel volume	7.6 l
Battery voltage	18 V
Type of product	Compressor

Accessories

Battery starter setHigh Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion batteryHigh Output™ Battery type MHB12	073811 MHB12