



Diamond burnishing tips, Tip radius: 0,4mm



Order data

Order number	291410 0,4
GTIN	4030741742125
Item class	29M

Description

Advantage:

Thanks to indexing there are 8 possibilities for using the diamond burnishing tips.
Surface quality $R_z < 1 \mu\text{m}$ possible.

Application:

For machining materials up to 65 HRC. Ideal for machining the surfaces of complex, continuous contours.

Accuracy:

Surface quality $R_z < 1 \mu\text{m}$ possible.

Note:

For detailed application recommendations please see the instruction handbook supplied.
Use the largest possible radius.

Technical description

Tip radius	0.4 mm
Type of product	Smooth rolling tool