

**Pressure test pump 1450, Type: 1****Order data**

| | |
|--------------|--------------|
| Order number | 814891 1 |
| GTIN | 095691500724 |
| Item class | 86A |

Description**Version:**

The pressure test pump model 1450 enables installations which must be free of leakages to be tested accordingly. The pump enables testing of systems with up to 50 bar (725 PSI) pressure.

- **Two-stage lever operation for quick filling of the system and pressure build-up.**
- **The pressure is retained automatically. No valve needs to be closed by hand.**
- **Filter at the inlet and outlet for better operating reliability.**
- **Aluminium- and carbon-reinforced PTFE piston pump for a longer working life.**
- **Dimensions L×W×H (720×220×240 mm); volume/stroke: 37.7 cm³.**

Application:

Particularly suitable for use in heating installations, compressed-air systems, cooling systems, oil installations, sprinkler systems and other hydraulic pipework with a small diameter.

Attention:

Leak-tightness tests may be performed only by using water, oil or a mixture of water and ethylene glycol.

Technical description

| | |
|------------------------|---------------|
| Hose length | 1.83 m |
| Width | 220 mm |
| Hose connection thread | 1/2 inch BSPP |
| maximum pressure | 50 bar |

Data sheet

| | |
|---------------------|----------------------|
| maximum temperature | 50 °C |
| Delivery per stroke | 37.7 cm ³ |
| Height | 240 mm |
| Length | 710 mm |
| Weight | 6.4 kg |
| Container volume | 13.6 l |
| Type of product | Test pump |