



## Holder for diamond burnishing tips Swivelling head, Shank size: 16-25



### Order data

Order number	291405 16-25
GTIN	4030741903182
Item class	29M

### Description

**Version:**

Swivelling tool head (adjustment range  $\pm 90^\circ$ ).

**Advantage:**

Surface quality  $R_z < 1 \mu\text{m}$  possible.

**Application:**

For machining materials up to 65 HRC. Ideal for machining the surfaces of complex, continuous contours.

For burnishing of **uninterrupted contours** (convex, concave, cylindrical, conical) and flat faces. Suitable even for applications up to the collar.

**Accuracy:**

Surface quality  $R_z < 1 \mu\text{m}$  possible.

**Supplied with:**

Shank size 16 including shank adaptor 20 mm  $\times$  20 mm and 25 mm  $\times$  25 mm.

**Attention:**

Diamond burnishing tips must be ordered separately!

**Note:**

For detailed application recommendations please see the instruction handbook supplied.

### Technical description

Shank size	16 - 25 mm
Type of product	Smooth rolling tool