

**Garant**
**Solid carbide T-slot cutter, semi-roughing, TiAlN, Ø DC × LC d11 × d11: 16X8 mm**

**Order data**

Order number	208034 16X8
GTIN	4045197269058
Item class	11X

**Description**
**Version:**

**With new high-performance coating** for very long tool life. The sides of the teeth are ground to give clearance and thus cannot jam in the component.

**Note:**

Suitable for milling T-slots according to DIN 650.

Feed at 50 %  $f_z$  until full engagement.

Type: NF

No. of teeth Z: 6

No. of teeth Z: 6

for T-slots DIN 650: 8 mm

Recess Ø  $D_1$ : 7 mm

Overall length L: 62 mm

Shank Ø  $D_s$ : 10 mm

Corner chamfer width at 45°: 0.2 mm

**Technical description**

Feed $f_z$ in steel < 900 N/mm <sup>2</sup>	0.034 mm
for T-slots DIN 650	8 mm
Cutting edge Ø $D_c$	16 mm
Corner chamfer width at 45°	0.2 mm
No. of teeth Z	6

Recess $\varnothing D_1$	7 mm
Shank $\varnothing D_s$	10 mm
Overall length L	62 mm
Type	NF
Flute length $L_c$	8 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 851
Milling profile	staggered teeth
Tolerance nominal $\varnothing$	d11
Helix angle	12 degrees
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Through-coolant	no
Shank tolerance	h6
Corner chamfer angle	45 degrees
Colour ring	green
Type of product	End mill