

**Garant**
**Solid carbide dovetail milling cutter Form D 60°, TiAlN, Ø js16 DC: 28 mm**

**Order data**

Order number	208038 28
GTIN	4045197270061
Item class	11X

**Description**
**Version:**

Angular tolerance  $\pm 8'$ .

**Note:**

For milling dovetails in tool making and machine building.

Feed at 50 %  $f_z$  until full engagement.

Through-coolant: no

No. of teeth Z: 10

No. of teeth Z: 10

Recess  $\varnothing D_1$ : 14 mm

Overall length L: 80 mm

Shank  $\varnothing D_s$ : 16 mm

Flute length  $L_c$ : 11 mm

Feed  $f_z$  in steel < 900 N/mm<sup>2</sup>: 0.045 mm

**Technical description**

Feed $f_z$ in steel < 900 N/mm <sup>2</sup>	0.045 mm
Recess $\varnothing D_1$	14 mm
No. of teeth Z	10
Cutting edge $\varnothing D_c$	28 mm
Shank $\varnothing D_s$	16 mm
Overall length L	80 mm

Flute length $L_c$	11 mm
Shape	D
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 1833
Tolerance nominal $\varnothing$	js16
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Through-coolant	no
Shank tolerance	h6
Corner chamfer angle	60 degrees
Colour ring	green
Type of product	End mill