

Garant
Solid carbide dovetail milling cutter Form C 60°, TiAlN, Ø js16 DC: 32 mm

Order data

Order number	208037 32
GTIN	4045197270009
Item class	11X

Description
Version:

Angular tolerance $\pm 8'$.

Note:

For milling dovetails in tool making and machine building.

Feed at 50% f_z until full engagement.

Through-coolant: no

No. of teeth Z: 9

No. of teeth Z: 9

Recess $\varnothing D_1$: 15 mm

Overall length L: 71 mm

Shank $\varnothing D_s$: 16 mm

Flute length L_c : 12.5 mm

Feed f_z in steel $< 900 \text{ N/mm}^2$: 0.045 mm

Technical description

No. of teeth Z	9
Cutting edge $\varnothing D_c$	32 mm
Feed f_z in steel $< 900 \text{ N/mm}^2$	0.045 mm
Recess $\varnothing D_1$	15 mm
Shank $\varnothing D_s$	16 mm
Overall length L	71 mm

Flute length L _c	12.5 mm
Shape	C
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 1833
Tolerance nominal Ø	js16
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Through-coolant	no
Shank tolerance	h6
Corner chamfer angle	60 degrees
Colour ring	green
Type of product	End mill