

Garant
Solid carbide dovetail milling cutter Form D 45°, TiAlN, Ø js16 DC: 28 mm

Order data

Order number	208036 28
GTIN	4045197269928
Item class	11X

Description
Version:

Angular tolerance $\pm 8'$.

Note:

For milling dovetails in tool making and machine building.

Feed at 50% f_z until full engagement.

Through-coolant: no

No. of teeth Z: 10

Recess $\varnothing D_1$: 14 mm

Overall length L: 80 mm

No. of teeth Z: 10

Shank $\varnothing D_s$: 16 mm

Flute length L_c : 7.5 mm

Feed f_z in steel $< 900 \text{ N/mm}^2$: 0.045 mm

Technical description

Recess $\varnothing D_1$	14 mm
Cutting edge $\varnothing D_c$	28 mm
No. of teeth Z	10
Feed f_z in steel $< 900 \text{ N/mm}^2$	0.045 mm
Shank $\varnothing D_s$	16 mm
Overall length L	80 mm

Flute length L _c	7.5 mm
Shape	D
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 1833
Tolerance nominal Ø	js16
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Through-coolant	no
Shank tolerance	h6
Corner chamfer angle	45 degrees
Colour ring	green
Type of product	End mill