

**Milling cutter lock screw through bored, DIN 6367, for mandrel Ø: 40mm****Order data**

Order number	309861 40
GTIN	4250122674214
Item class	30N

Description**Application:**

For attaching shell-type milling cutters.

Coolant supply via lateral holes.

Note:

Compatible with

- **Interface HSK, PSC.**
- **Interface SK and BT only with arbor form ADB.**

Technical description

for mandrel Ø	40 mm
Thread length	30 mm
Head Ø	52 mm
Thread M	M20
Head thickness	10 mm
Standard	DIN 6367

Type of product

Tightening screw