

**Milling cutter lock screw through bored, DIN 6367, for mandrel Ø: 60mm****Order data**

Order number	309861 60
GTIN	4250122681618
Item class	30N

Description**Application:**

For attaching shell-type milling cutters.

Coolant supply via lateral holes.

Note:

Compatible with

- **Interface HSK, PSC.**
- **Interface SK and BT only with arbor form ADB.**

Technical description

Head thickness	14 mm
for mandrel Ø	60 mm
Thread length	45 mm
Thread M	M30
Head Ø	75 mm
Standard	DIN 6367

Type of product

Tightening screw