

Garant**End mill, uncoated, Ø k10 DC: 5mm****Order data**

Order number	191530 5
GTIN	4045197103345
Item class	11W

Description**Version:**

Multi-flute end mill. End face recessed.

Eccentric relief ground.**Technical description**

Feed f_z for slot milling in steel < 750 N/mm ²	0.008 mm
No. of teeth Z	5
Cutting edge Ø D_c	5 mm
Shank Ø D_s	6 mm
Overall length L	68 mm
Flute length L_c	24 mm
Direction of infeed	horizontal and oblique
Shank	DIN 1835 B to h6
Tolerance nominal Ø	k10
Helix angle	30 degrees
Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	HSS Co 8
Standard	DIN 844 B

Type	N
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	83 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	25 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	23 m/min	K
CuZn	suitable only under restricted conditions	55 m/min	N
Uni	suitable		
wet maximum	suitable		